



HOLE GRID VACUUM TABLE

SAV 249.02SL

Use:

For clamping polymers and wood

Features:

- Base (6mm) and top plate (8mm) in aluminum
- Polyethylene body 15mm
- Vacuum holes with a pitch of 10x10 mm
- Holes diameter 5/0,3 mm
- For pipe outer diameter 10mm

Standard delivery:

- 1 vacuum table + connectors
- 1 supply pipe
- 1 martyr plate





For mounting the table on the machine table:

- 1. remove the base plate and attach it to the machine using the grooves in the plate (grooves always parallel to the width of the plate)
- 2. reassemble and screw the central and upper part back onto the base plate

| Dimensions en mm | | | | | 147-2-1-4 |
|------------------|--------------|--------------------|--------|----------|-----------------|
| Active length | Active width | Dimensions overall | Height | Nb holes | Weight in kg |
| 200 | 120 | 210x120 | 29 | 2 | 3,0 |
| 200 | 160 | 210x160 | 29 | 2 | 3,5 |
| 200 | 200 | 210x200 | 29 | 2 | 4,0 |
| 260 | 160 | 270x160 | 29 | 2 | 4,0 |
| 300 | 200 | 310x200 | 29 | 2 | 5,0 |
| 400 | 200 | 410x200 | 29 | 2 | 6,5 |
| 400 | 300 | 410x300 | 29 | 4 | 8,5 |
| 450 | 300 | 460x300 | 29 | 4 | 10,0 |
| 500 | 300 | 510x300 | 29 | 4 | 11,5 |
| 500 | 400 | 510x400 | 29 | 4 | 13,0 |
| 600 | 400 | 610x400 | 29 | 4 | 15,5 |
| 500 | 500 | 510x500 | 29 | 4 | 13,0 |
| 600 | 500 | 610x500 | 29 | 6 | 17,0 |
| 1000 | 400 | 1010x400 | 29 | 8 | 25,0 |
| 800 | 600 | 810x600 | 29 | 8 | 19,0 |
| 1000 | 500 | 1010x500 | 29 | 10 | 30,0 |
| 1000 | 600 | 1010x600 | 29 | 10 | 35,0 |



Base plate with grooves clamping across the width

Example of order:

Hole grid vacuum table Designation

SAV 249.02SL - 600 x 400 SAV N° - dimension